




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMENDED PCB LAYOUT
(GENERAL TOLERANCE IS ± 0.05)

NOTE:


1. MATERIAL:

- ① 1.1. HOUSING: THERMOPLASTIC, COLOR: BLACK, UL 94V-0;
- ② 1.2. CONTACT: COPPER ALLOY, $T=0.10\text{mm}$;
- ③ 1.3. SHELL: COPPER ALLOY, $T=0.12\text{mm}$.



2. FINISH:

- 2.1. CONTACT: GOLD FLASH PLATED ON MATING AREA, GOLD FLASH ON SOLDER TAILS, NICKEL UNDER PLATED OVER OF THE ALL;
- 2.2. SHELL: GOLD FLASH ON THE ALL, NICKEL PLATED UNDER.

- 3. 产品须符合环保RoHS和REACH标准。



Section: A-A



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.50	X':±2°	PART NO. ARF-003	TITLE: Ultra Small Surface Mount Coaxial CONN. USS RF SERIES		
X.X:±0.10	X.X':±1°				
X.XX:±0.05					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1