







PCB.WELDING DRAWING (TOLERANCE:±0.05)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Technical requirements	
Characteristic impedance	50Ω
Frequency range	0-3GHZ
Contact resistance	
Inner conductor	≤3mΩ
Outer conductor	≤2mΩ
Insulated resistance	≥5000MΩ
Salt spray time	48H
Separation force	≥0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	

1	铜座	1	黄铜	镀金
2	尖头母针	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5°	PART NO. ASMA-KE-PH135	TITLE: 偏脚 1.5—半螺内孔—H13.5	
X.X:±0.25	X.X':±1°			
X.XX:±0.15		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm			
MATERILA	— — —	CHED: Olvia		SCALE
FINISH	— — —	APPD: Ava		SHEET
			N:A	1/1