








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



PCB.WELDING DRAWING (TOLERANCE:±0.05)



Technical requirements	
Characteristic impedance	50Ω
Frequency range	0-6GHZ
Contact resistance	
Inner conductor	≤3mΩ
Outer conductor	≤2mΩ
Insulated resistance	≥5000MΩ
Salt spray time	48H
Separation force	≥0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	

1	半螺铜套	1	黄铜	镀金
2	母针	1	黄铜	镀金
3	绝缘体1	1	PTFE	
4	铜座	1	黄铜	镀金
5	绝缘体2	1	PTFE	
序号	名称	数量	材料	备注
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5°	PART NO. ASMA-KWE-ZH13	TITLE: 弯头—半螺内孔—H13*14.5—LW	
X.X:±0.25	X.X':±1°			
X.XX:±0.15				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		SCALE N:A
				SHEET 1/1