





SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

VER	MARK	PR. BY	DESCRIPTION	DATE

P/N	PIN	DIM. A	DIM. B
A20010530-2PB2111-H25C75	2*1	0.00	2.00
A20010530-4PB2111-H25C75	2*2	2.00	4.00
A20010530-6PB2111-H25C75	2*3	4.00	6.00
A20010530-8PB2111-H25C75	2*4	6.00	8.00
A20010530-10PB2111-H25C75	2*5	8.00	10.00
A20010530-12PB2111-H25C75	2*6	10.00	12.00
A20010530-14PB2111-H25C75	2*7	12.00	14.00
A20010530-16PB2111-H25C75	2*8	14.00	16.00
A20010530-18PB2111-H25C75	2*9	16.00	18.00
.....			
A20010530-80PB2111-H25C75	2*40	(PIN-1) x 2.0	(PIN) x 2.0

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
X.° ±0.30	X.° ±5°	PART NO. A20010530-XPB2111-H25C75	TITLE: 2.0PH H2.0 2xnPin SMT PC6.5 PA3.8 PB2.5 L8.0 6T	
X.X° ±0.25	X.X° ±1°			
X.XX° ±0.20	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SCALE N:A
				SHEET 1/1