

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)

<i>P / N</i>	<i>PIN</i>	<i>DIM. A</i>	<i>DIM. B</i>
<i>A20010130-2PB2113-H20C28</i>	<i>2*1</i>	<i>0. 00</i>	<i>2. 00</i>
<i>A20010130-4PB2113-H20C28</i>	<i>2*2</i>	<i>2. 00</i>	<i>4. 00</i>
<i>A20010130-6PB2113-H20C28</i>	<i>2*3</i>	<i>4. 00</i>	<i>6. 00</i>
<i>A20010130-8PB2113-H20C28</i>	<i>2*4</i>	<i>6. 00</i>	<i>8. 00</i>
<i>A20010130-10PB2113-H20C28</i>	<i>2*5</i>	<i>8. 00</i>	<i>10. 00</i>
<i>A20010130-12PB2113-H20C28</i>	<i>2*6</i>	<i>10. 00</i>	<i>12. 00</i>
<i>A20010130-14PB2113-H20C28</i>	<i>2*7</i>	<i>12. 00</i>	<i>14. 00</i>
<i>A20010130-16PB2113-H20C28</i>	<i>2*8</i>	<i>14. 00</i>	<i>16. 00</i>
<i>A20010130-18PB2113-H20C28</i>	<i>2*9</i>	<i>16. 00</i>	<i>18. 00</i>
<i>.....</i>	<i>.....</i>	<i>.....</i>	<i>.....</i>
<i>A20010130-80PB2113-H20C28</i>	<i>2*40</i>	<i>(PIN-1) x2. 0</i>	<i>(PIN) x2. 0</i>

GENERAL TOLERANCES UNLESS SPECIFIED		 HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.° ±0.30	X.° ±5°	PART NO.	TITLE:		
X.X° ±0.25	X.X° ±1°	A20010130-XPB2113-H20C28	2.0PH H2.0 2xnPin 180度 PC2.8 PA3.9 PB2.0 L8.7 6T		
X.XX°±0.20	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
			N:A	1/1	