

RoHs

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

VER	MARK	PR. BY	DESCRIPTION	DATE

P/N	PIN	DIM. A	DIM. B
A25411210-2PB2113-H25C30	2*1	0.00	2.54
A25411210-4PB2113-H25C30	2*2	2.54	5.08
A25411210-6PB2113-H25C30	2*3	5.08	7.62
A25411210-8PB2113-H25C30	2*4	7.62	10.16
A25411210-10PB2113-H25C30	2*5	10.16	12.70
A25411210-12PB2113-H25C30	2*6	12.70	15.24
A25411210-14PB2113-H25C30	2*7	15.24	17.78
A25411210-16PB2113-H25C30	2*8	17.78	20.32
A25411210-18PB2113-H25C30	2*9	20.32	22.86
.....			
A25411210-80PB2113-H25C30	2*40	(PIN-1) X2.54	(PIN) X2.54

GENERAL TOLERANCES
UNLESS SPECIFIED

X.° ±0.30	X.° ±5°
X.X° ±0.20	X.X° ±1°
X.XX° ±0.10	X.XX° ±0.5°





MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.	TITLE:
A25411210-XPB2113-H25C30	2.54PH H2.5 2xPin 90度 PC3.0 PA6.0 PB6.9 L13.8/18.8 6T 第四面
DESIGN: James	CUSTOMER
CHED: Talen	SIZE
APPD: Sophia	A4
	SCALE
	N:A

UNITS	MM
SHEET	1/1



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)