








REV.	ECN NO.	DR	DATE
A1	NEW	DR. Z	24. 8. 15



- 技术参数 SPECIFICATIONS:
- ◆ 线数: 2~12
Poies: 2~12
 - ◆ 材质: 常规尼龙 UL 94V-0或耐750/850度灼热丝
Material: Conventional nylon UL 94V-0 or 750/850 degree heat resistant wire
 - ◆ 颜色: 按订单要求
Colour: As per order requirements

7	SM-7R	15.0	20.5	18.2	4.00	18.35							
6	SM-6R	12.5	18.0	15.7	4.00	15.85	12	SM-12R	27.5	33.1	30.7	4.00	30.90
5	SM-5R	10.0	15.5	13.2	4.00	13.35	11	SM-11R	25.0	30.6	28.2	4.00	28.40
4	SM-4R	7.50	13.0	10.7	4.00	10.85	10	SM-10R	22.5	28.1	25.7	4.00	25.90
3	SM-3R	5.00	10.5	8.20	4.00	8.35	9	SM-9R	20.0	25.5	23.2	4.00	23.40
2	SM-2R	2.50	8.00	5.70	3.50	5.85	8	SM-8R	17.5	23.0	20.7	4.00	20.85
Circuits	Part No	Dim.A	Dim.B	Dim.C	Dim.D	Dim.E	Circuits	Part No	Dim.A	Dim.B	Dim.C	Dim.D	Dim.E

未注公差 TOLERANCE		FIRSTANGLE PROJECTION		CNCM 浙江成明电子科技有限公司 ZHEJIANG CHENGMING ELECTRONIC TECHNOLOGY CO.,LTD									
>50: ±0.65		拟制 DRAWING BY Ms Zheng 24-8-15		型号 PART NO:		SM-nR							
>20~50: ±0.5		确认 CHECKED BY Mr Xu 24-8-15		规格 SPECS:									
>5~20: ±0.3		审核 APPROVED BY Mr Lu 24-8-15											
SIZE	A4	UNIT	mm	SCALE	1:1	SHEET	1 OF 1	REV.	A1				