








If you have any questions, Don't hesitate to email sales@rj45jack.com, please!




NOTES:
MECHANICAL:
CAGES: COPPER ALLOY, THICKNESS 0.25MM.
PLATED: SELECTIVE PLATED OVER NICKEL
PLATED NICKEL 50u"~80u"
TEMPERATURE:
OPERATION: -40°C~+85°C
STORAGE: -40°C~+85°C
RoHS COMPLIANCE.

http://www.cd-tek.com		深圳磁联达电子有限公司			
QC : Inspection Item CPK : Cpk and SPC Control Item	DIMENSION IN mm [Inch]		Shen Zhen Cilianda Electronics Co., Ltd		
	TOLERANCE UNLESS OTHERWISE SPECIFIED		料号 PART NO:	图号 DWG NO.	
	.X± 0.25	X.*± 1*	SFP 46016000001 1x1Y	SFP 46016000001 1x1Y	
	.XX± 0.20	.X.*± 0.5*	名称 TITLE	SFP 46016000001 1x1Y	
	.XXX± 0.15				
核准 APPROVE	审核 CHECK	制图 DRAW	画法 PROJ.		页数 SHEET
QG.CHEN	X.YAN	SL.WANG	比例 SCALE	1:1	1 / 1
			图框 SIZE	A3	更改 REV
					A



1,2,3,11,14,16,17,18,19,20#孔直径为1.05mm;
4,5,7,8,9,10,12,13,15#孔直径为0.95mm;
6#孔直径为0.85mm;



DETAIL A(SCALE 2:1)

QC : Inspection Item CPK : Cp/Cpk and SPC Control Item	http://www.cd-tek.com		深圳磁联达电子有限公司			
	DIMENSION IN mm [Inch]		Shen Zhen Cilianda Electronics Co., Ltd			
	TOLERANCE UNLESS OTHERWISE SPECIFIED		料号 PART NO:		图号 DWG NO.	
	.X± 0.25	X.*± 1*	SFP 46016000001 1x1Y		SFP 46016000001 1x1Y	
	.XX± 0.20	.X*± 0.5*	名称 TITLE			
.XXX± 0.15		SFP 46016000001 1x1Y				
核准 APPROVE	审核 CHECK	制图 DRAW	画法 PROJ.		页数 SHEET	1 / 2
OG.CHEN	X.YAN	SL.WANG	比例 SCALE	1:1	图框 SIZE	A3
					更改 REV	A