




RoHS Compliant

更改 REV	设计内容 MODIFICATION	日期 DATE	制图 DRAW	核准 APPROVE
A	图面发行	2019/11/1	SL.WANG	QG.CHEN



NOTE:

MATERIAL:

1. TERMINAL: COPPER ALLOY

2. HOUSING: LCP UL 94V-0. COLOR: BLACK

MECHANICAL REQUIREMENT:

1. DURABILITY: 100 CYCLES MIN.

2. INSERTION AND EXTRACTION FORCE: 40N MAX & 11.5N M-ENVIRONMENTAL:

1. CONTACT RESISTANCE: 20 MILLIOHMS MAX INITIAL.



2. DIELECTRIC WITHSTANDING VOLTAGE: 300V AC/MIN.

3. OPERATION: -40°C~+85°C.


4. STORAGE: -55°C~+105°C.

5. REFLOW SOLDERING TEMPERATURE: 255~265° MAXIMUM FOR 5~10 SECONDS.

6. ROHS COMPLIANT





PCB LAYOUT




PART NUMBER: SFP+20P-03

GOLD PLATING U"
0-FU" 1-3U" 2-6U"
3-15U" 4-30U"

PLASTIC MATERIAL
0-LCP BLACK



MATING PCB



http://www.cd-tek.com		深圳磁联达电子有限公司				
QC : Inspection Item CPK : Cp/Cpk and SPC Control Item	DIMENSION IN mm [Inch]		Shen Zhen Cilianda Electronics Co., Ltd			
	TOLERANCE UNLESS OTHERWISE SPECIFIED		料 号 PART NO: SFP20 47030-00J191		图 号 DWG NO. SFP20 47030-00J191	
	.X± 0.25	X.*± 1*	名称 TITLE SFP20 47030-00J191			
	.XX± 0.20	.X.*± 0.5*				
	.XXX± 0.15					
核准 APPROVE OG.CHEN	审核 CHECK X.YAN	制图 DRAW SL.WANG	画法 PROJ. 比例 SCALE 1:1		页次 SHEET 1 / 1	
			幅面 SIZE A3	页次 REV A		

If you have any questions, Don't hesitate to email sales@j45jack.com, please!