






REV.	ECN NO.	DR	DATE
A1	NEW	DR.C	18.10.09




技术参数 SPECIFICATIONS:

- ◆ 线数: 2~16
Poles: 2~16
- ◆ 适用线规: AWG. #32~#26
Applicable Wire: AWG. #32~#26
- ◆ 额定电压: 125V DC/AC
Voltage Rating: 125V DC/AC
- ◆ 额定电流: 1.0A
Current Rating: 1.0A
- ◆ 耐压: 500V AC
Withstand Voltage: 500V AC
- ◆ 温度范围: -25° C~+85° C
Working Temperature: -25° C~+85° C
- ◆ 绝缘电阻: ≥500MΩ
Insulation Resistance: 500MΩ (MIN)
- ◆ 接触电阻: ≤30mΩ
Contact Resistance: 30mΩ (MAX)
- ◆ 材质/颜色: 尼龙 94V-0
Material: Nylon UL 94V-0
- ◆ 包装数量: 2000 pcs
Packaging Quantity: 2000 pcs



9	ZH-9Y	12.0	13.9	15.0		16	ZH-16Y	22.5	24.4	25.5
8	ZH-8Y	10.5	12.4	13.5		15	ZH-15Y	21.0	22.9	24.0
7	ZH-7Y	9.00	10.9	12.0		14	ZH-14Y	19.5	21.4	22.5
6	ZH-6Y	7.50	9.40	10.5		13	ZH-13Y	18.0	19.9	21.0
5	ZH-5Y	6.00	7.90	9.00		12	ZH-12Y	16.5	18.4	19.5
4	ZH-4Y	4.50	6.40	7.50		11	ZH-11Y	15.0	16.9	18.0
3	ZH-3Y	3.00	4.90	6.00		10	ZH-10Y	13.5	15.4	16.5
2	ZH-2Y	1.50	3.40	4.50						
Circuits		Part No	Dim.A	Dim.B	Dim.C	Circuits	Part No	Dim.A	Dim.B	Dim.C



未注公差 TOLERANCE	THIRD ANGLE PROJECTION
.X±0.30	X±2°
.XX±0.20	X±1°
.XXX±0.10	

CNCM 浙江成明电子科技有限公司
ZHEJIANG CHENGMING ELECTRONIC TECHNOLOGY CO.,LTD

拟制 DRAWING BY Mr Chen 18-10-09	审核 APPROVED BY Mr Zhao 18-10-09
确认 CHECKED BY Mr Lu 18-10-09	

DWG. NO.:	CNCM-ZH-nY	TITLE:	1.50mm Wire to Board
-----------	------------	--------	----------------------

型号 PART NO:

ZH-nY

SIZE	A4	UNIT	MM
------	----	------	----

SCALE	1:1	SHEET	1 OF 1	REV.	A1
-------	-----	-------	--------	------	----