




- 技术参数 SPECIFICATIONS:
- ◆ 线数: 2~16
Poies:2~16
 - ◆ 适用线规: AWG #28~#32
Applicable Wire: AWG #28~#32
 - ◆ 材质: 尼龙/灼热丝750° UL94V-0
Material: Nylon/Glowing wire 750 °
UL94V-0
 - ◆ 颜色: 按订单要求
Colour: As per order requirements

线数 Circuits	型号 Part No	尺寸			线数 Circuits	型号 Part No	尺寸		
		Dim.A	Dim.B	Dim.C			Dim.A	Dim.B	Dim.C
2	1.25-2Y	/	2.90	4.25	10	1.25-10Y	11.25	12.90	14.25
3	1.25-3Y	2.50	4.15	5.50	11	1.25-11Y	12.50	14.15	15.50
4	1.25-4Y	3.75	5.40	6.75	12	1.25-12Y	13.75	15.40	16.75
5	1.25-5Y	5.00	6.65	8.00	13	1.25-13Y	15.00	16.65	18.00
6	1.25-6Y	6.25	7.90	9.25	14	1.25-14Y	16.25	17.90	19.25
7	1.25-7Y	7.50	9.15	10.50	15	1.25-15Y	17.50	19.15	20.50
8	1.25-8Y	8.75	10.40	11.75	16	1.25-16Y	18.75	20.40	21.75
9	1.25-9Y	10.00	11.65	13.00					

未注公差 TOLERANCE		 THIRD ANGLE PROJECTION		 浙江成明电子科技有限公司 ZHEJIANG CHENGMING ELECTRONIC TECHNOLOGY CO.,LTD						
>35: ±0.65		拟制 DRAWING BY Wang 24-01-13		DWG NO: CNCM-1.25 TITLE: 1.25mm Wire to Board 型号 PART NO: 1.25-nY						
>20~35: ±0.5		确认 CHECKED BY Xu 24-01-13								
>10~20: ±0.4		审核 APPROVED BY Lu 24-01-13								
>0~10: ±0.3										
SIZE	A4	UNIT	MM	SCALE	1:1	SHEET	1 OF 1	REV.	A1	