











修正(标记)	描述	日期



P. C. B LAYOUT TOP VIEW



尺寸 类型	A
	3.00±0.20
	2.50±0.20
	2.30±0.20
	2.00±0.20



主要技术性能		公 差	设 计	部 门 会 签			DC-003WT -1.3	
额定电负荷	DC 30V\1A	X.±0.30	版 次		装配部		市场部	
接触电阻	≤0.03Ω	.X±0.20	日 期	2014.06.13	注塑部			
绝缘电阻	≥100MΩ	.XX±0.10	材 料		冲压部			
耐 压	AC500V(50Hz)/min	.XXX±0.05	工 艺		视 角	重 量	比 例	DC电源插座
插 拔 力	3-30N	X.±5°	数 量				1:1	浙江创都电子科技有限公司
使用温度范围	-30-70°C	.X±2°	审 核		共 6 张		第 1 张	
使 用 寿 命	5000次	.XX±1°	核 准					