





SCHEMATIC



技术特性:

使用条件: $-30 \sim 70^{\circ}$

额定负荷: DC30V 10A

接触电阻: $\leq 0.02 \Omega$

绝缘电阻: $\geq 100\text{m}\Omega$ DC250V



耐 压: AC250V (50Hz) /min

插拔力: 3~15N

寿命: 5000次

PCB LAYOUT

TOP VIEW (TOLERANCE:±0.05)



5	平片	1	磷铜0.65 δ=0.50mm	D. Cu/Sn
4	插针PIN	1	H59黄铜棒(Y)	D. Cu/Sn
3	外壳	1	H62黄铜带 δ=0.4mm	D. Cu/Sn
2	弹片	1	磷铜0.65 δ=0.30mm	D. Sn/Sb
1	基座	1	PA9T	黑
序号	名称	数量	材 料	备 注

GENERAL TOLERANCES			
0.X	± 0.30	X. ^o	$\pm 3^{\circ}$
0.XX	± 0.20		
0.XXX	± 0.10	X.X ^o	$\pm 1^{\circ}$
UNIT	SIZE	SCALE	
MM	A4	1:1	

DRAWN		C	TITLE: 电源插座		
DESIGN		PART NO.		DC-0102-10A-**-9T	
CHECKED		PRODUCT NO.			
		DRAWING NO.			
APPROVED		UNIT: mm SCALE: 1:1 REV: 01-1 SHT: 1 OF 1			

浙江创都电子科技有限公司

	01	2022.04.26	NEW DRAWING RELEASE		
ECN NO	REV	DATE	DESCRIPTION	MDF'D	APP'D