




RoHS Component

“*” Pivot Dimension

PO(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
009	16.33	24.99	30.81	19.28
015	24.66	33.32	39.14	27.51
025	38.38	47.04	53.04	41.28
037	54.84	63.50	69.32	57.71



NOTICE :

1. ELECTRICE:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 5AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.at 500V DC

DIELECTRIC STRENGTH: 500V AC RMS for 1Minute

OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

INSULATOR: PBT+30% G. F (UL94V-0)

CONTACT: COPPER ALLOY

CONTACT PLATED:GOLD FIASH OVER NICKEL

SHELL: SPCC

SHELLPLATED:NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE:

X.X ±0.38

X.XX ±0.25

X.XXX ±0.13

X° ±5° X.X° ±2°

UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

DATE :

2009. 08. 22

PART NAME:

DB XP 母 焊线式传统铆合

CHECKED BY:

DATE :

2009. 08. 22

DRAW NO.

DB-M-*P-HX-GK

PART NO.

APPROVED BY:

DATE :

2009. 08. 22

REMARK

MOLD NO.