







87654321



PCB LAYOUT  
TOP VIEW (TOLERANCE:±0.05)



SCHEMATIC



### 技术特性:

使用条件: - 3 0 ~ 7 0 °  
额定负荷: D C 3 0 V 0 . 5 A  
接触电阻: ≤ 0.03 Ω  
绝缘电阻: ≥ 100M Ω DC250V  
耐 压: AC500V (50Hz) /min  
插 拔 力: 3~20N  
寿 命: 5000次

|    |     |    |                     |     |
|----|-----|----|---------------------|-----|
| 6  | 盖 板 | 1  | 酚醛纸板T=1.6           | 黄   |
| 5  | 插 针 | 1  | H59黄铜棒              | 铜锡  |
| 4  | 平 片 | 1  | H62黄铜带 (Y) δ=0.30mm | 铜锡  |
| 3  | 弯 片 | 1  | H62黄铜带 (Y) δ=0.30mm | 铜锡  |
| 2  | 弹 片 | 1  | 65Mn 锰钢带δ=0.20mm    | 锡锑  |
| 1  | 基 座 | 1  | PBT                 | 黑   |
| 序号 | 名 称 | 数量 | 材 料                 | 备 注 |

| GENERAL TOLERANCES |       |       |     |
|--------------------|-------|-------|-----|
| 0.X                | ±0.30 | X.°   | ±3° |
| 0.XX               | ±0.20 |       |     |
| 0.XXX              | ±0.10 | X.X°  | ±1° |
| UNIT               | SIZE  | SCALE |     |
| MM                 | A4    | 1:1   |     |

DRAWN

DESIGN

CHECKED

APPROVED

C

TITLE: 电源插座

PART NO.

DC-022A-2.0-MN

PRODUCT NO.

DRAWING NO.

UNIT: mm SCALE: 1:1 REV: 01-1 SHT: 1 OF 1

浙江创都电子科技有限公司

| ECN NO. | REV | DATE       | DESCRIPTION         | MDF'D | APP'D |
|---------|-----|------------|---------------------|-------|-------|
|         | 01  | 2021.12.22 | NEW DRAWING RELEASE |       |       |

87654321