









PCB LAYOUT
TOP VIEW (TOLERANCE:±0.05)



SCHEMATIC



技术特性:

使用条件: -30~70℃
额定负荷: DC30V 0.5A
接触电阻: ≤0.03Ω
绝缘电阻: ≥100MΩ DC250V
耐压: AC500V(50Hz)/min
插拔力: 3~20N
寿命: 5000次

6	盖板	1	PBT	黄
5	插针	1	H59黄铜棒	铜锡
4	平片	1	H62黄铜带(Y) δ=0.30mm	铜锡
3	弯片	1	H62黄铜带(Y) δ=0.30mm	铜锡
2	弹片	1	65Mn 锰钢带 δ=0.25mm	锡锡
1	底座	1	PBT	黑
序号	名称	数量	材料	备注

GENERAL TOLERANCES			
0.X	±0.30	X°	±3°
0.XX	±0.20		
0.XXX	±0.10	X.X°	±1°
UNIT	SIZE	SCALE	
MM	A4	1:1	

DRAWN
DESIGN
CHECKED
APPROVED

C

TITLE: 电源插座

PART NO.

DC-016-2.0-MN

PRODUCT NO.

DRAWING NO.

UNIT: mm SCALE: 1:1 REV: 01-1 SHT: 10F1

浙江创都电子科技有限公司

ECN NO.	REV	DATE	DESCRIPTION	MDF'D	APP'D
	01	2021.12.22	NEW DRAWING RELEASE		