




PCB LAYOUT TOP VIEW



CIRCUIT DIAGRAM

技术要求

使用条件: -40 ~ 55°C
额定负荷: DC 24V 5A
接触电阻: ≤ 0.03Ω
绝缘电阻: ≥ 100MΩ DC250V
耐压: AC 500V (50Hz) /min
插拔力: 3 ~ 20N
机械寿命: 5000次

Marker	Describe			Data	DSND
UNSPECIFIED TOLERANCE	≤4 ±0.15	4-16 ±0.20	≥16 ±0.30	ANGULAR ±5°	

No.	PART NAME	QTY	MATERIAL (THICK, COLOR)	REMARK
⑥	HOUSING PH-DC-0027-Z2	1	PBT (Black)	
⑤	COVER PC-DC-0027-Z2	1	PBT (Black)	
④	PIN MP-DC-0027-30QxC	1	H59 Φ=3.0	CuSn-Plated
③	TERMINAL MT-DC-0027-3QxC	1	BRASS t=0.50	Ag-Plated
②	TERMINAL MT-DC-0027-2QxC	1	PHOSPHOR BRONZE t=0.25	Ag-Plated
①	TERMINAL MT-DC-0027-1QxC	1	BRASS t=0.50	Ag-Plated
DSND	Chuyunfeng	DATE	2009.11.04	SCALE: 2 : 1
CHKD		DATE		VIEW:
APVD		DATE		UNIT: mm
				NAME: DC POWER JACK
				DC-0062-**