




PCB LAYOUT TOP VIEW



CIRCUIT DIAGRAM

技术要求

使用条件: $-40 \sim 55^\circ\text{C}$
 额定负荷: DC 24V 5A
 接触电阻: $\leq 0.03\Omega$
 绝缘电阻: $\geq 100\text{M}\Omega$ DC250V
 耐压: AC 500V (50Hz) /min
 插拔力: 3 ~ 20N
 机械寿命: 5000次

Marker	Describe	Data	DSND
UNSPECIFIED TOLERANCE	≤ 4 ± 0.15	4-16 ± 0.20	≥ 16 ± 0.30

No.	PART NAME	QTY	MATERIAL (THICK, COLOR)	REMARK
⑥	HOUSING PH-DC-0027-Z2	1	PBT (Black)	
⑤	COVER PC-DC-0027-Z2	1	PBT (Black)	
④	PIN MP-DC-0027-30QxC	1	H59 $\varnothing=3.0$	CuSn-Plated
③	TERMINAL MT-DC-0027-3QxC	1	BRASS $t=0.50$	Ag-Plated
②	TERMINAL MT-DC-0027-2QxC	1	PHOSPHOR BRONZE $t=0.25$	Ag-Plated
①	TERMINAL MT-DC-0027-1QxC	1	BRASS $t=0.50$	Ag-Plated
DSND	Chuyunfeng	DATE	2009.11.04	SCALE: 2 : 1
CHKD		DATE		VIEW:
APVD		DATE		UNIT: mm
				NAME: DC POWER JACK
				DC-0062-5A**