




RoHS Component

“*” Pivot Dimension

P0(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
009	16.92	24.99	30.81	19.28
015	25.25	33.32	39.14	27.51
025	38.96	47.04	53.04	41.28
037	55.42	63.50	69.32	57.71



NOTICE :

1. ELECTRIC:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 3AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.at 500V DC

DIELECTRIC STRENGTH: 500V AC RMS for 1Minute

OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

INSULATOR: PBT+30% G.F(UL94V-0)

CONTACT: COPPER ALLOY

CONTACT PLATED:GOLD FIASH OVER NICKEL

SHELL: SPCC

SHELLPLATED:NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: X.X ±0.38 X.XX ±0.25 X.XXX ±0.13 X° ±5° X.X° ±2° UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY :	DATE : 2009. 08. 22	PART NAME: DB XP 公 焊线式传统铆合	
	CHECKED BY:	DATE : 2009. 08. 22	DRAW NO.	DB-G-*P-HX-GK
	APPROVED BY:	DATE : 2009. 08. 22	PART NO.	
			REMARK	
			MOLD NO.	