





SCHEMATIC (NON-SHORTING)

SS-22F12-GXXX

直柄 G-Switch P/N

G=020 (2.0) G=030 (3.0)
G=040 (4.0) G=050 (5.0)
G=055 (5.5) G=060 (6.0)
G=065 (6.5) G=070 (7.0)
G=075 (7.5) G=080 (8.0)
G=085 (8.5) G=090 (9.0)
G=095 (9.5) G=100 (10.0)

G-Switch Specification:
RATING (额定值): DC50V 0.5A
CONTACT RESISTANCE 接触电阻: $\leq 70m\Omega$
INSULATION RESISTANCE 绝缘电阻: $\geq 100m\Omega$
DIELECTRIC STRENGTH 耐电压: AC 500V for 1 minute
TIMING (时间特性): SHORTING



RoHS
Compliant
2002/95/EC



G-Switch Electronic Technology CO.,Ltd.

Unless otherwise specified, Tolerance:
X. ± 0.30
X.x ± 0.20
X.xx ± 0.15
X.xxx ± 0.10
Angles $\pm 3^\circ$

DESIGN 陈锋枫
CHECKED
APPROVED

DATE 2016.05.29
DATE
DATE

TITLE:

SS-22F12-GXXX

<http://www.dg-switch.com>
TEL:0769-82388879

REV.: X1 SCALE: 4:1 UNIT: mm
SIZE: A4 SHEET: 1/1