




技术指标(Technical Index):

1. 温度范围(Temperature range): -25° C~+85° C.
2. 额定电压(Rated voltage): 150V, AC, DC.
3. 额定电流(Rated current): 1.0A AC, DC.
4. 接触电阻(Contact resistance): ≤20mΩ .
5. 耐压值(Withstanding voltage): 500V AC/minute.
6. 绝缘电阻(Insulation resistance): ≥500MΩ.
7. 产品料号(Product material No.):

WT125F1L-***-***
NO OF CKT (产品PIN数) * * * * * 流水码
Plating (电镀方式) * * * * * Packing (包装方式)
1: 端子全金 (G/F OVERALL) T: TUBE 管装
2: 端子全亮锡 C: TAPE & REEL WITH COVER
加吸盖卷装

序号	品名	材质
①	DF16立式贴片WTB胶芯	LCP UL94V-0 本色
②	DF16立式贴片WTB端子	铜合金/表面镀锡
③	DF16立式贴片WTB焊片	铜合金/表面镀锡
④	DF16立式贴片WTB吸盖	LCP UL94V-0 本色

CKT	A	B	C	D
2	1.25	3.05	6.10	7.45
3	2.50	4.30	7.35	8.70
4	3.75	5.55	8.60	9.95
5	5.00	6.80	9.85	11.20
6	6.25	8.05	11.10	12.45
7	7.50	9.30	12.35	13.70
8	8.75	10.55	13.60	14.95
9	10.00	11.80	14.85	16.20
10	11.25	13.05	16.10	17.45
11	12.50	14.30	17.35	18.70
12	13.75	15.55	18.60	19.95
13	15.00	16.80	19.85	21.20
14	16.25	18.05	21.10	22.45
15	17.50	19.30	22.35	23.70
16	18.75	20.55	23.60	24.95
18	21.25	23.05	26.10	27.45
20	23.75	25.55	28.60	29.95
30	36.25	38.05	41.10	42.45

ZGWD 浙江温达电子有限公司
ZHEJIANG WENDA ELECTRONICS CO., LTD

品名 (TITLE)	制图 (DR)	ANLAN
1.25 Pitch DF16立式贴片WTB	校对 (CHKD)	田峰
料号 (DWG.NO)	审核 (APPD)	黄志明
WT125F1L-***-***	张数 (SHEET)	1 OF 1
比例 (SCALE)	单位 (UNITS)	mm
	尺寸 (SIZE)	A4
	版本 (REV)	A



一般公差 (TOLERANCE)
X ±0.50 .XX ±10
X ±0.20 .XXX ±05
ANGLES ±1°