

版次	变更摘要	日期
0	新产品发行	2023/02/23
1	料号更新	2024/12/13

序号	品名	材质
①	PHD卧贴WTB胶芯	LCP UL94V-0 本色
②	PHD卧贴(连续)端子	铜合金/表面镀锡

1

2

3

4

5







1

2

3

4

5



2P 结构样式

CKT	A	B
2*2	2.0	6.0
2*3	4.0	8.0
2*4	6.0	10.0
2*5	8.0	12.0
2*6	10.0	14.0
2*7	12.0	16.0
2*8	14.0	18.0
2*9	16.0	20.0
2*10	18.0	22.0
2*11	20.0	24.0
2*12	22.0	26.0
2*13	24.0	28.0
2*14	26.0	30.0
2*15	28.0	32.0
2*16	30.0	34.0
2*18	34.0	38.0
2*20	38.0	42.0

技术指标(Technical Index):

- 工作温度(Temperature range): -25° C~+85° C.
- 适用线规(Apply to gauge): AWG#28~#24
- 额定电压(Rated voltage): 250V DC/AC(rms).
- 额定电流(Rated current): 3.0A AC,DC.
- 接触电阻(Contact resistance): ≤20mΩ.
- 耐压值(Dielectricwithstanding voltage): 800V AC/minute.
- 绝缘电阻(Insulation resistance): ≥1000MΩ.
- 产品料号(Product material No.):

WB200D1W—** *—***
NO OF CKT(产品PIN数) 流水码
Plating(电镀方式) Packing(包装方式)
0:端子全雾锡 R:TAPE & REEL卷装
(Terminal all mist tin) P:PE袋装
1:端子全金
(Terminal G/F OVER ALL)
3:端子全亮锡
(Terminal all bright tin)



一般公差(TOLERANCE)
X: ±.50 .XX ±.10
X: ±.20 .XXX ±.05
ANGLES ±1°

ZGWD 浙江温达电子有限公司
ZHEJIANG WENDA ELECTRONICS CO., LTD

品名 (TITLE) 2.0 Pitch D型双排卧贴WTB业务图	制图 (DR) Anlan
料号 (DWG.NO) WB200D1W-****-***	校对 (CHKD) 田峰
比例 (SCALE)	审核 (APPD) 黄志明
单位 (UNITS) mm	张数 (SHEET) 1 OF 1
尺寸 (SIZE) A4	版本 (REV) A