





A B C D E F

版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2021/01/23	①	PHD 立贴WTB胶芯	LCP UL94V-0 米色
1	料号更新	2024/11/12	②	PHD 立贴(连绕)端子	铜合金/表面镀锡





## 技术指标(Technical Index):

- 工作温度(Temperature range): -25° C ~ +85° C.
- 适用线规(Apply to gauge): AWG#28~#22
- 额定电压(Rated voltage): 250V DC/AC(rms).
- 额定电流(Rated current): 3.0A AC, DC.
- 接触电阻(Contact resistance): ≤20mΩ.
- 耐压值(Dielectric withstand voltage): 800V AC/minute.
- 绝缘电阻(Insulation resistance): ≥1000MΩ.
- 产品料号(Product material No.):

WB200D1L—\*\* \* \*—\*\*\*

NO OF CKT(产品PIN数) 流水码  
 Plating(电镀方式) Packing(包装方式)  
 1:端子全金(G/F OVERALL)  
 3:端子全亮锡  
 P:袋装  
 R:不加盖卷装  
 C:加盖卷装



2P 结构样式

RoHS

一般公差(TOLERANCE)  
 X. ±50 .XX ±10  
 X. ±20 .XXX ±05  
 ANGLES ±1°

品名 (NAME)	制图 (DR)	Anlan
2.0 Pitch D型双排立贴WTB业务图	校对 (CHKD)	田峰
审核 (APPD)		
WB200D1L-*****	黄志明	
比例 (SCALE)	单位 (UNITS)	张数 (SHEET) SIZE REV
mm		1 OF 1 A4 A