

项目 Mapx	变更内容 Modification	日期 Date	修改人 Draw	核准 Approve
------------	----------------------	------------	-------------	---------------

规格说明:Specifications:

电气特性:Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
- 2.额定电压: Voltage Rating
30V DC
- 3.接触电阻: Contact Resistance
30 milliohms MAX
- 4.耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 5.绝缘阻抗: Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力: Connector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retention
1.0kgf(MIN)

原材料:Material:

- 1.塑胶:Housing:
Hing Temperature Ternmaplastics,

- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:


- 1.端子:Contact: Plated Gold in Mating Area,
Tin On Solder Talls

端子四周镀50U”(MIN)锡,镀金区域镀100—200U”镀金1U”

2.外壳:Shell:

铜壳四周镀80U”(MIN)锡

Nickel Plating



成品图		公差一览表		日期		单位		制图		DWG NO.	
公差一览表		TOLERANCE UNLESS OTHERWISE		DATE		MM		DRAWING		F23-35AF4U1078-112	
. X ± 0.15		X. ± 5°		2016.10.20		1:1		LAYOUT		零件4件共7.8(90度)底座	
. XX ± 0.05		. X ± 2°		审核		比例		DESIGN		版本	
. XXX ± 0.02		. XX ± 1°		核准		角法		VER		AO	
		APPROVE				角法				页	
										数	
										006	
										SHEET	

广东富盈兴业精密科技实业有限公司