








RoHS2.0+REACH



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

SPECIFICATION:

1. CURRENT RATING: 5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -25 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES



CONNECTOR
FRONT EDGE

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

6	接地片	NO PLATED	SUS316L-1/2H T=0.12mm	1
5	中夹片	NO PLATED	SUS301R-H T=0.15mm	1
4	SHELL	50u"min (可焊镍) 环保 盐雾24H	SUS304 1/2H T=0.30mm	1
3	CCNTACT	C2680 Ni:50min Tin: 100~180u "Au:1u"Min 环保 盐雾24H	C2680 T=0.15mm	1
2	CCNTACT	C2680 Ni:50min Tin: 100~180u "Au:1u"Min 环保 盐雾24H	C2680 T=0.15mm	1
1	HOUSING	HIGH TEMPERATURE PLASTIC	LCP E130i 30%GF	1
NO.	DESCRIPTION	FINISH/COLOR	MATERIAL	Q'TY

5.0					
4.0					
3.0					
2.0					
1.0					
NO.	DATE	DESCRIPTION	DRAWING		

DRAWING:	GENERAL TOLERANCE	
Frank	.X:=±0.30 .X':=±2° .XX:=±0.25 .XX':=±1° .XXX:=±0.15 .XXX':=±0.5°	
CHECKED:	UNIT: MM	PROJECTION:
yangjie	SCALE: 1:1	
APPROVAL:	SHEET: 1/1	

CHIN-BAN
Electronic Technology

DESCRIPTION:	USB C TYPE 母座单排16Pin LCP蓝色
PART NO:	USBC1-AF-045
OLD CODE:	
DRAWING NO:	
REV: 1.0	
SIZE: A4	