


A	Dept	晨翔2.54mm排母, 2*5PIN, 弯插, Y型端子, 镀半金, 黑胶, 胶高8.5mm			REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty				A	NEW RELEASE	JLZ 08/24/24'			
	DC	晨翔料号: DS1024-2x5R2								
	ED									
	IE									
B	ISO				备注: 1. 电性说明: 1.1 接触阻抗: 20毫欧最大。 1.2 耐压: 600伏交流电一分钟。 1.3 绝缘阻抗: 1000兆欧最小。 1.4 额定电流: 3安。 2. 环境特性: 2.1 工作温度: -40~+105° C。 3. 材料: 3.1 端子: H62黄铜, 镀半金。 3.2 胶芯: PBT, 黑色, 阻燃。 4. 产品符合RoHS环保要求。					B
	PD									
	R&D									
	SD									
	QA									
C	QC				10.16±0.25 0.60*0.4t 2.54±0.1  6.0~6.5 建议对插针长 13.20±0.3 8.50 0.80 5.00 12.6 2.54 3.5 10.16 2.54 2.54 ø1.02 PCB板孔参考尺寸 公差: ±0.05					C
	QE									
D					GENERAL TOLERANCE X. ±0.60 .X ±0.38 .XX ±0.25 ANGLE TOLERANCE X. ±5° .X ±3° .XX ±2° DRAWING TYPE CUSTOMER SCALE 1:1 SHEET 1 OF 1 DRAWING NO. C-DS1024-XXXXX-A					D
E					PROJECTION  TITLE FEMALT HEADER PITCH 2.54mm R/A DOUBLE ROW TYPE SHEET SIZE A4 SERIES DS1024 SERIES  晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD					E
F										F
G										G
H										H

此图提供的信息来自宁波晨翔电子有限公司并且是保密的。禁止向收件人以外的任何一方披露信息。本文包含的知识产权及其权利(包括但不限于商标、专利、版权, 商业秘密和技术知识) 仅由晨翔或其附属公司拥有。未经晨翔事先书面同意, 严禁未经授权的使用或修改。 晨翔可以自行决定强制执行其知识产权; 不履行或延迟行使这些权利并不构成对这些权利的放弃。