




RoHS2.0+REACH

- NOTES:
SPECIFICATION:
1. CURRENT RATING: 5A MAX
 2. VOLTAGE: 100 VAC
 3. TEMPERATURE RANGE: -30 °C ~ 85 °C
 4. CONTACT RESISTANCE: 40 MILLIONHM MAX
 5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
 6. INSERTION FORCE : 5N~20N
 7. UNMATING FORCE: 8N~20N
 8. DURABILITY: 10,000 CYCLES



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

6	接地片	SUS316L-1/2H T=0.12mm	清洗	1PCS
5	中夹片	SUS301R-H T=0.15mm	清洗	1PCS
4	SHELL	SUS304 1/2H T=0.30mm	NI 50u" Plated	1PCS
3	CONTACT	C7025	Ni:50u"Min,Tin:80u" Min Au:1u"	1SET
2	CONTACT	C7025	Ni:50u"Min,Tin:80u" Min Au:1u"	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	LCP E130i 30%GF BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

.X:= ± 0.30

.XX:= ± 0.25

.XXX:= ± 0.15

.X*:= $\pm 2^\circ$

.XX*:= $\pm 1^\circ$


.XXX*:= $\pm 0.5^\circ$

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: USB C TYPE 母座单排16Pin沉板1.6mm LCP黑

PART NO: USBC1-AF-048

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4