

项目 Mapx	变更内容 Modification	日期 Date	修改人 Draw	批准 Approve
------------	----------------------	------------	-------------	---------------

规格说明: Specifications:

电气特性: Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触电阻: Contact Resistance
30 milliohms MAX
- 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

- 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
- 端子保持力: Terminal Retention
1.0kgf(MIN)

原材料: Material:

- 塑壳: Housing:
Hing Temperature Thermoplastics,
- 端子: Contact: Copper Alloy C2680
- 外壳: Shell: Copper Alloy C2680/SPCC




电镀: Finish:

- 端子: Contact: Plated Gold in Mating Area:
Tin On Solder Talls
- 端子: 50U”(MIN) 镀, 镀金区域镀 100—200U” 镀金 1U”

2. 外壳: Shell:

铜壳四周镀 80U”(MIN) 镀

Nickel Plating



A

B

由 Autodesk 教育版产品制作

E

F

广东富盈兴业精密科技实业有限公司

成品图 MANUFACTURE DWG		公差一覽表 TOLERANCE UNLESS OTHERWISE	
X±0.15	X±5°	DATE	2016.10.20
X±0.05	X±2°	CHECKED	审核
XXX±0.02	XX±1°	APPROVE	批准
UNIT	MM	DRAWING	图例
SCALE	1:1	DESIGN	设计
NAME	LUFU	NAME	品名
VER	版本	VER	版本
AO	页数	AO	页数
SHEET	003	SHEET	003

6

7

8

A

B

E

F

1

2

3

4

5

6

7

8