



RoHS2.0+REACH



NOTES:

SPECIFICATION:

1. CURRENT RATING: 5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -25 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES



CONNECTOR
FRONT EDGE

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

6	接地片	NO PLATED	SUS316L-1/2H T=0.12mm	1
5	中夹片	NO PLATED	SUS301R-H T=0.15mm	1
4	SHELL	50u"min (可焊镍) 环保 盐雾24H	SUS304 1/2H T=0.30mm	1
3	CCNTACT	C7025 Ni:50min Tin: 100~180u "Au:1u"Min 环保 盐雾24H	C7025 T=0.15mm	1
2	CCNTACT	C7025 Ni:50min Tin: 100~180u "Au:1u"Min 环保 盐雾24H	C7025 T=0.15mm	1
	HOUSING	HIGH TEMPERATURE PLASTIC	LCP E130i 30%GF	1
NO.	DESCRIPTION	FINISH/COLOR	MATERIAL	Q'TY

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:


GENERAL TOLERANCE

.X:=±0.30 .X':=±2°
.XX:=±0.25 .XX':=±1°
.XXX:=±0.15 .XXX':=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1:1



SHEET: 1/1

CHIN-BAN
Electronic Technology

DESCRIPTION: USB C TYPE 母座单排16Pin LCP黑

PART NO: USBC1-AF-043

REV: 1.0

OLD CODE:

DRAWING NO:

SIZE: A4

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING