

1		2		3		4		5		6		7		8	
A	Dept	晨翔2.54mm排母, 2*7PIN, 弯插, Y型端子, 镀半金, 黑胶, 胶高8.5mm								REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty									A	NEW RELEASE	JLZ 08/24/24'			
	DC	晨翔料号: DS1024-2x7R2													
	ED														
	IE														
B	ISO														B
	PD														
	R&D														
	SD														
	QA														
C	QC														C
	QE														
D															D
E															E
F															F
G															G
H															H

晨翔2.54mm排母, 2*7PIN, 弯插, Y型端子, 镀半金, 黑胶, 胶高8.5mm

晨翔料号: DS1024-2x7R2

0.60*0.4t

15.24±0.25

2.54±0.1

6.0~6.5

建议对插针长

18.28±0.3

8.50

0.80

5.00

12.6

2.54

3.5

15.24

2.54

2.54

φ1.02

PCB板孔参考尺寸
公差: ±0.05

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	FEMALT HEADER PITCH
X.	±0.60	X.	±5°	UNITS	mm		2.54mm R/A DOUBLE ROW TYPE
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1024 SERIES
.XX	±0.25	.XX	±2°				
DRAWING TYPE		CUSTOMER		 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			
SCALE		1:1					
DRAWING NO.		C-DS1024-XXXXX-A					