


A	Dept	1	晨翔2.54mm排母, 1*2PIN, 弯插, Y型端子, 镀半金, 黑胶, 胶高8.5mm				REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty	1					A	NEW RELEASE	JLZ 08/24/24'			
	DC	1	晨翔料号: DS1024-1x2R2									
	ED	1										
	IE	1										
B	ISO	1										B
	PD	1										
	R&D	1										
	SD	1										
	QA	1										
C	QC	1										C
	QE	1										
D												D
E												E
F												F
G												G
H												H

晨翔2.54mm排母, 1*2PIN, 弯插, Y型端子, 镀半金, 黑胶, 胶高8.5mm

晨翔料号: DS1024-1x2R2



建议对插针长

PCB孔位布局参考
公差: ±0.05

备注:

1. 电性说明:

1.1 接触阻抗: 20毫欧最大。

1.2 耐压: 600伏交流电一分钟。

1.3 绝缘阻抗: 1000兆欧最小。

1.4 额定电流: 3安。

2. 环境特性:

2.1 工作温度: -40~+105° C。

3. 材料:

3.1 端子: H62黄铜, 镀半金。

3.2 胶芯: PBT, 黑色, 阻燃。

4. 产品符合RoHS环保要求。

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm Female Header					
X.	±0.60	X.	±5°	UNITS	mm		R/A Single Row Type					
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1024 SERIES					
.XX	±0.25	.XX	±2°	 晨翔电子有限公司								
DRAWING TYPE									CUSTOMER			
SCALE									1:1	SHEET	1 OF 1	
DRAWING NO.									C-DS1024-XXXXX-A			
					CONNFLY CONNFLY ELECTRONIC CO. LTD							