

项目 Mapx	变更内容 Modification	日期 Date	修改人 Draw	批准 Approve
------------	----------------------	------------	-------------	---------------

规格说明: Specifications:

电气特性: Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触电阻: Contact Resistance
30 milliohms MAX
- 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

- 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
- 端子保持力: Terminal Retention
1.0kgf(MIN)

原材料: Material:

- 塑壳: Housing:
Hing Temperature Thermoplastics,
- 端子: Contact: Copper Alloy C2680
- 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:




- 端子: Contact: Plated Gold in Mating Area:
Tin On Solder Talls
- 端子四周镀50U”(MIN) 锡, 镀金区域镀100—200U” 镀金1U”

- 外壳: Shell:
铜壳四周镀80U”(MIN) 锡

Nickel Plating

广东富盈兴业精密科技实业有限公司

成品图 MANUFACTURE DWG		公差一覽表 TOLERANCE UNLESS OTHERWISE	
X $\pm$ 0.15	X $\pm$ 5°	日期 DATE	2016.10.20
X $\pm$ 0.05	X $\pm$ 2°	审核 CHECKED	
XXX $\pm$ 0.02	.XX $\pm$ 1°	批准 APPROVE	
		图例 SCALE	1 : 1
		视图 VIEW	
		DWG NO.	FY23-35AF4J1082-013
		品名 NAME	铜壳插座后脚8.2(90度) 转接
		版本 VER	AO
		页次 SHEET	003



RECOMMENDED P.C.B LAYOUT