

12345678

Dept

Qty

DC

1

ED

1

IE

1

ISO

1

PD

1

R&D

1

SD

1

QA

1

QC

1

QE

1

晨翔2.00mm排母, 1*2PIN, 直插, 镀金, 黑胶, 胶高4.3mm

晨翔料号: DS1026-01-1x2S8BV

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 08/31/24'		

1

2

3

4

5

6

7

8

4.50±0.3

2.50

4.30

2.70±0.2

0.50*0.2t

2.00±0.1

2.00

Ø0.80

PCB孔位尺寸参考
公差: ±0.05

备注:

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐压: 500伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

1.4 额定电流: 1.5安

2. 环境特性:

2.1 工作温度: -40~+105° C

3. 材料:

3.1 端子: H62黄铜, 镍底镀金

3.2 胶芯: PA-9T, 黑色, 阻燃

4. 产品符合RoHS环保要求

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE
X.	±0.60	X.	±5°	UNITS	mm	2.00 Female Header V/T Type
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES DS1026-01 SERIES
.XX	±0.25	.XX	±2°			
DRAWING TYPE		CUSTOMER		晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD		
SCALE		1:1 SHEET 1 OF 1				
DRAWING NO.		C-DS1026-01-XXXXX-A				

12345678