







REV.	ECN NO.	DR	DATE
A1	NEW	DR. W	24.11.15



P. C. B LAYOUT
TOLERANCE: ±0.05

线数	型号	尺寸				
		Dim. A	Dim. B	Dim. C	Dim. D	Dim. E
2	HY-2A立贴	/	8	4.75	3.5	7.55
3	HY-3A立贴	4	10	6.75	3.2	9.55
4	HY-4A立贴	6	12	8.75	6.6	11.55
5	HY-5A立贴	8	14	10.75	5.5	13.55
6	HY-6A立贴	10	16	12.75	7.5	15.55
7	HY-7A立贴	12	18	14.75	9.5	17.55
8	HY-8A立贴	14	20	16.75	11.5	19.55
9	HY-9A立贴	16	22	18.75	13.5	21.55
10	HY-10A立贴	18	24	20.75	15.5	23.55
11	HY-11A立贴	20	26	22.75	17.5	25.55
12	HY-12A立贴	22	28	24.75	19.5	27.55
13	HY-13A立贴	24	30	26.75	21.5	29.55
14	HY-14A立贴	26	32	28.75	23.5	31.55
15	HY-15A立贴	28	34	30.75	25.5	33.55
16	HY-16A立贴	30	36	32.75	27.5	35.55

- 技术参数 SPECIFICATIONS:
- ◆ 材质: LCP UL94V-0+黄铜
 - ◆ Material: LCP UL94V-0+Brass
 - ◆ 镀层: 亮锡
 - ◆ Plating: Tinning
 - ◆ 颜色: 按订单要求
 - ◆ Colour: As per order requirements

未注公差 TOLERANCE		CNCM 浙江成明电子科技有限公司 ZHEJIANG CHENGMING ELECTRONIC TECHNOLOGY CO.,LTD		型号 PART NO: HY-nALTCM	
	拟制 DRAWING BY Ms Wang 24-11-15				
	确认 CHECKED BY Mr Xu 24-11-15				
	审核 APPROVED BY Mr Lu 24-11-15				
规格 SPECS:		规格	SPECS:		
SIZE		UNIT	mm	SCALE	1:1
>50: ±0.65		>20~50: ±0.5		>0~5: ±0.3	
>50: ±0.65		>20~50: ±0.5		>0~5: ±0.3	
SIZE		A4			