





RoHS2.0+REACH



- NOTES:
SPECIFICATION:
1. CURRENT RATING: 5A MAX
 2. VOLTAGE: 100 VAC
 3. TEMPERATURE RANGE: -30 °C ~ 85 °C
 4. CONTACT RESISTANCE: 40 MILLIONHM MAX
 5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
 6. INSERTION FORCE : 5N~20N
 7. UNMATING FORCE: 8N~20N
 8. DURABILITY: 10,000 CYCLES

PIN ASSIGNMENT:

Pin No.	Signal Name	Pin No.	Signal Name
A1	CND	B12	CND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	CND	B1	CND

5	中夹片	STAINLESS STEEL	No Plated	1PCS
4	SHELL	STAINLESS STEEL	Ni 50u" Plated	1PCS
3	CONTACT	COPPER ALLOY	Au, Sn SEE TABLE Ni50u" Plated	1SET
2	CONTACT	COPPER ALLOY	Au, Sn SEE TABLE Ni50u" Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

.X:=±0.30

.XX:=±0.25

.XXX:=±0.15

.X*:=±2°

.XX*:=±1°


.XXX*:=±0.5°

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: USB C TYPE母16pin P距0.70mm, 长度10.45mm

PART NO: USBC1-AF-058

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING