







RoHS2.0+REACH



SPECIFICATIONS:

Contact current Rating:

1.8 Amperes for pin1&pin4.

0.25 Amperes other contacts

Dielectric Withstanding Voltage:AC 100V(RMS)

Insulation resistance:100Megohms Minimum.

Contact Resistance:

30mΩ Max for pin1&pin4

50mΩMax for other contacts

Mechanical Characteristics:


Mating Force:35 Newtoms.Maximum

Unmating Force:10 Newtoms.Mlimum.

Operating Temperature:-40 °C+85 °C

Pin Number	Signal Name	Pin Number	Signal Name
1	VBUS	5	SSRX-
2	D-	6	SSRX+
3	D+	7	GND
4	GND	8	SSTX-
Shell	Shield	9	SSRT+

ITEM	PART NAME	Material	Q'TY	REMARK
1	4P Semi-	Housing LCP&PBT	1	Black &Blue UL94V-0
2	manufactured Goods	Contact COPPER ALLOY	4	T=0.25 Plating Gld/Tin
3	5P Semi-	Housing LCP&PBT	1	Black &Blue UL94V-0
4	manufactured Goods	Contact COPPER ALLOY	5	T=0.25 Plating Gld/Tin
5	Shell	Stainless Steel	1	T=0.3



DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

.X:=±0.30

.X':=±2°

.XX:=±0.25

.XX':=±1°

.XXX:=±0.15

.XXX':=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1:1

⊙

SHEET: 1/1

⊙

CHIN-BAN
Electronic Technology

DESCRIPTION: USB3.0 AF侧贴直脚有边

PART NO: USB30-AF-006

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4