






RoHS2.0+REACH



P.C.B LAYOUT



NOTES:

1.MECHANICAL:

MATING: 35N MAX.

WITHDRAWAL: 10N MIN.

DURABILITY: 1500 CYCLES MIN.

2.ELECTRICAL:

CURRENT: 1.5A MAX

VOLTAGE: 30V MAX

WITHSTANDING VOLTAGE: 500V AC

CONTACT RESISTANCE: 30 mΩ MAX

INSULATION RESISTANCE: 1000MΩ MIN

3.ENVIRONMENTAL

TEMPERATURE RANGE -55°C ~ +85°C

Table:

ITEM	PART NAME	Q'TY	Material
1	SHELL	1	SPCC,T=0.35,Ni PLATED 80U*Min
2	SEMI-PRODUCT	1	PBT+30%GF,BLACK,GOLD FLASH
3	CONTACT	4	C2680R-H,GOLD FLASH

5.0			
4.0			
3.0			
2.0			
1.0			
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:

Frank

CHECKED:

yangjie

APPROVAL:

GENERAL TOLERANCE

.X:=±0.30

.XX:=±0.25

.XXX:=±0.15

.X°:=±2°

.XX°:=±1°


.XXX°:=±0.5°

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: USB AM 90° DIP(IM) 不帶倒扣 4.5 0.35 PBT黑

PART NO: USBC1-AM-035

OLD CODE:

DRAWING NO:

REV: 1.0

SIZE: A4