

A	Dept	晨翔2.00mm排针, 2*40PIN, 弯插, 镀金, 黑胶, 胶高2.0mm, 针长10.5/14.5mm	REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty		A	NEW RELEASE	JLZ 08/31/24'			
	DC	1						
	ED	1						
	IE	1						
B	ISO	晨翔料号:DS1025-06-2x40P8BR1-B						B
	PD							
	R&D							
	SD							
	QA							
C	QC							C
	QE							
D								D
E								E
F								F
G								G
H								H

晨翔2.00mm排针, 2*40PIN, 弯插, 镀金, 黑胶, 胶高2.0mm, 针长10.5/14.5mm

晨翔料号:DS1025-06-2x40P8BR1-B

ISO

PD

R&D

SD

QA

QC

QE

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐压: 500伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

1.4 额定电流: 1.5安

2. 环境特性:

2.1 工作温度: -40~+105° C

3. 材料:

3.1 端子: H65黄铜, 镍底镀金

3.2 胶芯: PA-9T, 黑色, 阻燃

4. 产品符合RoHS环保要求

PCB孔位布局参考
公差: ±0.05

晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD