

1		2		3		4		5		6		7		8		
A	Dept	晨翔2.00mm排母, 2*3Pin, 直插, U型端子镀金, 黑胶, 胶高4.3mm								REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A	
	Qty									A	NEW RELEASE	JLZ 08/31/24'				
	DC	晨翔料号: DS1026-05-2x3S8BV														
	ED															
	IE															
B	ISO														B	
	PD															
	R&D															
	SD															
	QA															
C	QC														C	
	QE															
D																D
E																E
F																F
G																G
H																H

晨翔2.00mm排母, 2*3Pin, 直插, U型端子镀金, 黑胶, 胶高4.3mm

晨翔料号: DS1026-05-2x3S8BV

ISO 1

PD 1

R&D 1

SD 1

QA 1

QC 1

QE 1

6.50±0.3

4.60

4.30

2.70±0.2

2.00±0.1

0.50*0.2t

4.00±0.2

2.00

2.00

4.00

2.00

Ø0.80

PCB孔位布局参考
公差: ±0.05

GENERAL TOLERANCE

ANGLE TOLERANCE

PROJECTION

UNITS

SHEET SIZE

TITLE

FEMALE HEADER PITCH 2.0mm
Vertical Trthrough TYPE

SERIES

DS1026-05 SERIES

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1026-05-XXXXX-A

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD