



A	Dept	1	晨翔2.00mm排针, 1*5PIN, 弯插, 镀金, 黑胶, 胶高2.0mm, 针长10.5mm			REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A																																																											
	Qty	1				A	NEW RELEASE	JLZ 08/31/24'																																																														
	DC	1																																																																				
	ED	1																																																																				
	IE	1																																																																				
B	ISO	1	晨翔料号:DS1025-02-1x5P8BR1-B								B																																																											
	PD	1																																																																				
	R&D	1																																																																				
	SD	1																																																																				
	QA	1																																																																				
C	QC	1									C																																																											
	QE	1																																																																				
D												D																																																										
E	备注: 1. 电性说明: 1.1 接触阻抗: 20毫欧最大 1.2 耐压: 500伏交流电一分钟 1.3 绝缘阻抗: 1000兆欧最小 1.4 额定电流: 1.5安 2. 环境特性: 2.1 工作温度: -40~+105° C 3. 材料: 3.1 端子: H65黄铜, 镍底镀金 3.2 胶芯: PA-9T, 黑色, 阻燃 4. 产品符合RoHS环保要求											E																																																										
F												F																																																										
G	PCB孔位布局参考 公差: ±0.05											G																																																										
H	<table><tr><td colspan="2">GENERAL TOLERANCE</td><td colspan="2">ANGLE TOLERANCE</td><td>PROJECTION</td><td></td><td>TITLE</td><td colspan="2" rowspan="2">2.00mm PIN HEADER R/A TYPE SINGLE ROW</td></tr><tr><td>X.</td><td>±0.60</td><td>X.</td><td>±5°</td><td>UNITS</td><td>mm</td><td colspan="3">SHEET SIZE</td><td>A4</td><td>SERIES</td><td colspan="2" rowspan="5">DS1025-02 SERIES</td></tr><tr><td>.X</td><td>±0.38</td><td>.X</td><td>±3°</td><td colspan="5" rowspan="4"> 晨翔电子有限公司</td></tr><tr><td>.XX</td><td>±0.25</td><td>.XX</td><td>±2°</td></tr><tr><td colspan="2">DRAWING TYPE</td><td colspan="7">CUSTOMER</td></tr><tr><td>SCALE</td><td>1:1</td><td>SHEET</td><td>1 OF 1</td></tr><tr><td colspan="2">DRAWING NO.</td><td colspan="8">C-DS1025-02-XXXXX-A</td></tr></table>											GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.00mm PIN HEADER R/A TYPE SINGLE ROW		X.	±0.60	X.	±5°	UNITS	mm	SHEET SIZE			A4	SERIES	DS1025-02 SERIES		.X	±0.38	.X	±3°	 晨翔电子有限公司					.XX	±0.25	.XX	±2°	DRAWING TYPE		CUSTOMER							SCALE	1:1	SHEET	1 OF 1	DRAWING NO.		C-DS1025-02-XXXXX-A								H
												GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE			2.00mm PIN HEADER R/A TYPE SINGLE ROW																																																	
												X.	±0.60	X.	±5°	UNITS	mm	SHEET SIZE					A4	SERIES	DS1025-02 SERIES																																													
												.X	±0.38	.X	±3°	 晨翔电子有限公司																																																						
												.XX	±0.25	.XX	±2°																																																							
DRAWING TYPE		CUSTOMER																																																																				
SCALE	1:1	SHEET	1 OF 1																																																																			
DRAWING NO.		C-DS1025-02-XXXXX-A																																																																				