







RoHS2.0+REACH



NOTES:
SPECIFICATION:

1. CURRENT RATING: 5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES
9. DRAWINGS MARKED "⊗" FOR FAI DIMENSION.
10. DRAWINGS MARKED "*" FOR QIP DIMENSION.

PIN ASSIGNMENT:

Pin No.	Signal Name	Pin No.	Signal Name
A1	CND	B12	CND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	CND	B1	CND

5	中夹片	STAINLESS STEEL	No Plated	1PCS
4	SHELL	STAINLESS STEEL	Ni 50u" Plated	1PCS
3	CONTACT	COPPER ALLOY	Au, Sn SEE TABLE N150u" Plated	1SET
2	CONTACT	COPPER ALLOY	Au, Sn SEE TABLE N150u" Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

5.0				DRAWING: Frank	GENERAL TOLERANCE							
4.0					.X:=±0.30 .XX:=±0.25 .XXX:=±0.15	.X*:=±2° .XX*:=±1° .XXX*:=±0.5°						
3.0				CHECKED: yangjie	UNIT: MM	PROJECTION:				DESCRIPTION: USB C TYPE 母座16pin P距0.70mm 外壳长9.30mm		
2.0					SCALE: 1:1					PART NO: USBC1-AF-061		REV: 1.0
1.0				APPROVAL:	SHEET: 1/1		OLD CODE:		SIZE: A4			
NO.	DATE	DESCRIPTION	DRAWING			DRAWING NO:						