





RoHS2.0+REACH



NOTES:


NOTES:
SPECIFICATION:

1. CURRENT RATING: 5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES




PIN ASSIGNMENT:

Pin No.	Signal Name	Pin No.	Signal Name
A1	CND	B12	CND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	CND	B1	CND



5	中夾片	STAINLESS STEEL	No Plated	1PCS
4	SHELL	STAINLESS STEEL	Ni 50u" Plated	1PCS
3	CONTACT	COPPER ALLOY	Au, Sn SEE TABLE NI50u" Plated	1SET
2	CONTACT	COPPER ALLOY	Au, Sn SEE TABLE NI50u" Plated	1SET
1 NO.	HOUSING DESCRIPTION	HIGH TEMPERATURE PLASTIC MATERIAL	BLACK REMARKS	1PCS QTY

5.0				DRAWING: Frank	GENERAL TOLERANCE				
4.0					.X:=±0.30 .XX:=±0.25 .XXX:=±0.15 .X*:=±2° .XX*:=±1° .XXX*:=±0.5°				
3.0				CHECKED: yangjie	UNIT: MM	PROJECTION:	DESCRIPTION: USB C TYPE母16pin P距0.70mm, 外壳鱼叉脚		
2.0					APPROVAL:	SCALE: 1:1		PART NO: USBC1-AF-059	REV: 1.0
1.0				SHEET: 1/1		OLD CODE:			
NO.	DATE	DESCRIPTION	DRAWING					DRAWING NO:	