



1 2 3 4 5 6 7 8

项目	说明	日期	绘图人	批准

A



规格说明:Specifications:
电气特性:Electrical:
 1. 额定电流: Current Rating
 1.5A/contact terminal
 2. 额定电压: Voltage Rating
 30V DC
 3. 接触电阻: Contact Resistance
 30 millionms MAX
 4. 耐电压: Dielectric Withstanding Voltage:
 500 V AC AT Sea Level
 5. 绝缘阻抗: Insulation Resistance:
 1000MEGA ohms MIN

物理特性:Mechanical:
 1. 握力: Connector Mate and Unmate Force
 Mate force: 3.57kgf(MAX)
 Unmate force: 1.02kgf(MIN)
 2. 端子保持力: Terminal Retention
 1.0kgf(MIN)

原材料:Material:
 1. 壳体:Housing
 Hing Temperature Thermoplastics,
 2. 接触:Contact:Copper Alloy C2680
 3. 外壳:Shell: Copper Alloy C2680/SPCC
电镀:Finish:
 1. 接触:Contact: Plated Gold in Mating Area
 Tin On Solder Tails
 端子四周镀50U”(MIN)镀,镀金区域镀100–200U”镀金1U”
 2. 外壳:Shell:
 铜壳四周镀80U”(MIN)镀

Nickel Plating

广东富盈兴业精密科技实业有限公司



制造
工程图

设计
工程图

制图
工程图

F

MANUFACTURE DRAWING
TOLERANCE UNLESS OTHERWISE
X±0.15 X±5° DATE 2016.10.20 UNIT MM DRAWING DWG NO. FY23-35AF41Z/002-023
XX±0.05 X±2° CHECKED SCALE 1:1 DESIGN LIUFU NAME 胡伟强 8.2 (90K) #
XXX±0.02 .XX±1° APPROVE VIEW AO VER SHEET 001



RECOMMENDED P.C.B LAYOUT

F E D C B A

1 2 3 4 5 6 7 8