



剖视图: B-B



剖视图: A-A

NOTES:

1. MATERIAL:

MOLDING: LCP UL94 V-0
 CONTACT: COPPER ALLOY.
 GOLD PLATED Min ON CONTACT AREA.
 SHELL: SUS304-H, T=0.30±0.03mm
 NICKEL PLATING OVER ALL.

2. MECHANICAL:

INSERTION: 5~20N.
 EXTRACTION: 8~20N AFTER TEST.
 DURABILITY: 3000 CYCLES

3. ELECTRICAL:



CURRENT: 3A FOR VBUS;
 1.25A FOR GND PIN.
 0.25A FOR OTHER.

VOLTAGE: 20 V MAX
 WITHSTANDING VOLTAGE: 100V AC R.M.S.
 CONTACT RESISTANCE: 40mΩ MAX.
 INSULATION RESISTANCE: 100MΩ MIN.

4. ENVIRONMENTAL

TEMPERATURE RANGE -30°C ~ +85°C

B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND
PIN	SIGNAL NAME

				APPROVALS		DATE	TITLE: DETECTOR SWITCHS
				DRAWN	LIUCAN		
				CHECKED			
				APPROVALS			PART NO. TYPE-C-31-M-16
				TOLERANCES ARE	30~以上 ±0.30	ANGLE	UNIT: mm
					10~30 ±0.20		SCALE: 1:1
					5~10 ±0.15	±2°	PROJ: 
					~ 5 ±0.10		DRAWING NO. 
ECN NO.	REV.	DATE.	NEW	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1
			DESCRIPTION.				