




安装尺寸 MOUNTING MEASUREMENT



技术要求 Specification:

- 1、材质 Material: Rubber shell: PA66 UL94V-2(0) PIN: H65 (Plating: NiSn)
- 2、额定电流 Current rating: 9A max
- 3、额定电压 Voltage rating: 300V AC/DC
- 4、温度范围 Temperature range: -25℃ to +85℃
- 5、接触电阻 Contact resistance: ≤15mΩ
- 6、绝缘电阻 Insulation resistance: ≥1000MΩ
- 7、耐压 Withstand voltage: 1500V AC/minute
- 8、插针的固定力 Fixing force of pins: ≥25N
- 9、适配的插头 Adaptable plug: HX42000-RN(5557)
- 10、适用基板厚度 Applicable PC board thickness: 1.6mm

A	0	4.2	8.4	12.6	16.8	21.0	25.2	29.4	33.6	37.8	42.0	46.2
B	5.4	9.6	13.8	18.0	22.2	26.4	30.6	34.8	39.0	43.2	47.4	51.6
尺寸 孔位	2	4	6	8	10	12	14	16	18	20	22	24

未注公差表 UNTOLERANCE TABLE		设计 DRAWN BY		王鹏程		产品名称 PRODUCT NAME		针座 WAFER			
≤3	± 0.1	审核 CHECKED BY		郑建银		产品型号 PRODUCT MODEL		5569-A			
≤10	± 0.2	批准 APPROVED BY		沈才义		红星代号 HONGXING NO		HX42003-A			
≤20	± 0.3	日期 DATE		2022. 12. 12		 浙江红星电业有限公司 Zhejiang Hongxing Electrical Co., Ltd.					
≤35	± 0.4	视图 VIEW		单位 UNIT						页码 SHEET	
≤50	± 0.5	mm		1/1							
≤75	± 0.6										
≤100	± 0.8										
ANGLE	± 5°										