




所用物料均符合ROHS标准

标“*”为重点检验尺寸

PO(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
015	16.92	24.99	30.81	19.28
026	25.25	33.32	39.14	27.51
044	38.96	47.04	53.04	41.28



NOTICE :

1. ELECTRICE:

DIELECTRIC RATING: 300V
CONTACT CURRENT RATING: 3AMP
CONTACT RESISTANCE: 15mΩ MAX.
INSULATION RESISTANCE: 1000MΩ MIN.AT 500V DC
DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE
OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

INSULATOR: PBT+30% G. F(UL94V-0)
CONTACT: COPPER ALLOY
CONTACT PLATED:GOLD FIASH OVER NICKEL
SHELL: SPCC
SHELL PLATED:NICKEL/TIN

TOLERANCE: XX ±0.38 XX ±0.25 XXX ±0.13 X° ±5° X.X° ±2° UNIT: mm [inch] SCALE:1:1	DRAWN BY :	DATE : 2011. 01. 05	PART NAME: HDB XP 公 焊线式传统铆合
	CHECKED BY:	DATE : 2011. 01. 05	DRAW NO.
	APPROVED BY:	DATE : 2014. 11. 05	PART NO.
		REMARK	
		MOLD NO.	