






CUSTOMER


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




- 1: Au 9/f
2: Au 3u"
4: Au 15u"
5: Au 30u"



两排端子



SECTION-A-A



After Mating

NO.	PART NAME	MATERIAL	FINISH	Q' TY
5	GROUND	SUS 304		1PCS
4	MID-PLATE	SUS 301		1PCS
3	OUTER SHELL	SUS 304	Ni:30u"Min.	1PCS
2	CONTACTS	C7025 TMO3	Contact area:Ni:50u";Au 1u"; Solder area: Ni:50u";Au 6/F; Other area:Ni:50u";	24PCS
1	HOUSING	LCP	BLACK, UL 94V-0	1PCS

TOLERANCE			NAME(INTENDED USE)	
X.X	±0.30	X.X	±10°	PART NO.
.XX	±0.20	.X	± 8°	CF 24P沉板0.8 80G
.XXX	±0.10	.XX	± 5°	
UNITS	mm	DESIGN:	ZXM	DRAWG NO.
MATERILA	----	CHED:		F723-68TC24F279-08-50
FINISH	-----	APPD:		

Guangdong FUYOU Precision Electronic Technology Co.,LTD.	
SCALE	SHEET
1:1	1/2
REV.	A