






FH201-9



Fuse holder for overload protection

Screw-in mounting


Rating: 15A 250VAC (UL,CUL)

Fuse:Ø6.0x30mm




Cap:Bayonet type


Panel thickness:4.5mm max



Operating Temperature:0°C~+85°C



CUT-OUT



MATERIAL:

Housing:PBT,UL rated 94V2 min
Bayonet:PBT,UL rated 94V2 min
Terminal:Brass,silver or tin plated
Nut:PBT,UL rated 94V2 min

				公差 TOLERANCES	.X±0.3 .XX±0.15	角度 ANGLE ± 1°	单位 DIMENSION UNIT		mm.
				版本 VERSION	A1	比例尺 SCALE	1:1	日期 DATE	2019.10.16
A1	重新整理发行	2019.10.16	N/A						
A0	New Issue	2009.02.26	N/A						
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO	核准 APPROVED BY	核对 CHECKED BY	Z.H.B.	绘图 DRAWN BY	王立权	
							品名 TITLE	图号 DRAWING NO	
							FH201-9-PZ	FH201-9-PZ_A1	