







PARTS DIMENSION TABLE

parts no.	DIM. a	DIM. b	inner thread
1	4.8	11.8	4#40
2	5.8	12.0	4#40
3	4.8	11.8	M3
4	5.8	11.8	M3
5	4.8	11.8	M2.6
6	5.8	12.0	M2.6
7	6.0	12.0	4#40



NOTES:
 INSULATION RESESTANCE(MIN.):1000MOHMS
 CURRENT RATING(MAX.): 3amp AC/DC
 WITHSTANDING VOLTAGE:1000VAC
 CONTACT RESISTANCE(MAX.)30m chms
 OPERATION TEMPERATURE:-55~+105°
 MATERIAL:
 CONTACT: PHOSPHOR BRONZE
 INSULATION:PBT+30%GLASS FIBER.UL 94V-0
 SHELL;STEEL
 NOTICE: THE DIMENSION MAKED WITH " * "
 MUST BE CONTROLLED BY QC.

POS.	A	B	C	D	E	G
9	30.80	24.99	16.92	19.00	15.60	4.0/4.6
15	39.23	33.28	25.38	27.70	24.60	4.0/4.6
25	53.05	47.04	38.84	41.10	38.10	4.0/4.6
37	69.45	63.50	55.43	57.30	54.45	4.0/4.6

ECN BO.		new		2015/5/3		A		瀚源	
DESIGNED		CHECKED		APPROVAL		DATE.		REV.	
Mikey		Tom		Jerry		PART NAME		DP-XXPM-XX	
						MODEL NAME		DP-XXPM-XX	
						3RD ANGLE PROJ		HanElectricity Co.,LTD	
						UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	
						SCALT: 1/2		SCALE: 3:1	
						FILE.NO.			