







MATERIALS AND FINISH

SHELL : STEEL MATERIAL, NICKEL FINISHED

DIMPLES ON PLUG ONLY

INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR

CONTACT MATERIAL : BRASS

CONTACT FINISH : SELECTIVE GOLD FLASH
GROUNDING BRACKET : BRASS MATERIAL, TIN FINISHED

JACK SCREWS : STEEL MATERIAL , NICKEL FINISHED
WITH #4-40 THREADED ASSEMBLED

ELECTRICAL CHARACTERISTICS


CONTACT CURRENT RATING : 5.0 AMPS

CONTACT RESISTANCE : 30 MILLIOHMS MAX.

DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.

INSULATION RESISTANCE : 5000 MEGAOHMS MIN.

TEMPERATURE RATING : $-55^{\circ}\text{C} \sim +105^{\circ}\text{C}$

PARTS DIMENSION TABLE

parts no.	DIM. a	DIM. b	inner thread
1	4.8	11.8	4#40
2	5.8	12.0	4#40
3	4.8	11.8	M3
4	5.8	11.8	M3
5	4.8	11.8	M2.6
6	5.8	12.0	M2.6
7	6.0	12.0	4#40

D M R H - X X P F - X X

TYPE

PIN

F:Female M:Male

Color:W:white B:black BL:blue

No. of Contact	A	B	C	E
09	30.90	24.99	16.34	2.29
15	39.24	33.32	24.76	2.29
25	53.10	47.04	38.40	2.29
37	69.50	63.50	54.89	2.41

_____		new			2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.			DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	DMRH-XXPF-XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:			X. ±0.25		
			MODEL NAME	DMRH-XXPF-XX				X.x ±0.20		
			3RD ANGLE PROJ			HanElectricity Co.,LTD				